

	<b>protocol A</b>	<b>protocol B</b>
B0 / T	3.0	1.5
no. of GD	49	52
no. of b = 0	1	4
b / s/mm <sup>2</sup>	1000	1000
slices	52	55
in-plane matrix	96 x 128	128 x 128
slice thickness / mm	2.2	2.8
pixel size / mm <sup>2</sup>	2.2 x 2.2	2.0 x 2.0
TE	85	95
TR	7600	8000

**Supplementary Table 1: Scan parameters for the different protocols.**